



HSTPYG075025FRL, Heat Shrink, Thin Wall, Yellow/Green

By Burndy
Catalog # [HSTPYG075025FRL](#)

.75" ID Min (Issued), .313" ID Max (Recovered), Thin Wall, Yellow/Green, 25-Foot Reel

Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 3:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

Current

Voltage Rating 600 V

Dimensions



Height	0.03 in
Width	0.75 in
Length	300 in
Dimensions	300 in x 0.75 in x 0.03 in

General

Product Type	Polyolefin Thin Wall Heat Shrink
Color	Yellow/Green
UPC	621945696051

Logistics

Carton Quantity	4
-----------------	---

Product Assets

[Catalog \[English\]](#)