



HSTPYL0094100FRL, Heat Shrink Tubing, Thin Wall, Yellow

By Burndy
Catalog # [HSTPYL0094100FRL](#)



.094" ID Min (Issued), .047" ID Max (Recovered), Thin Wall, Yellow, 100-Foot Reel

Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

Current

Voltage Rating 600 V

Dimensions

Height	0.02 in
Width	0.094 in
Length	1200 in
Dimensions	1200 in x 0.094 in x 0.02 in

General

Product Type	Polyolefin Thin Wall Heat Shrink
Color	Yellow
UPC	621945691834

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalog \[English\]](#)