



HSTPYL018725FRL, Heat Shrink Tubing, Thin Wall, Yellow

By Burndy
Catalog # [HSTPYL018725FRL](#)

.187" ID Min (Issued), .093" ID Max (Recovered), Thin Wall, Yellow,
25-Foot Reel

Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

Dimensions

Height	0.02 in
Width	0.187 in



Length	300 in
Dimensions	300 in x 0.187 in x 0.02 in

General

Color	Yellow
UPC	621945693227

Logistics

Pallet Quantity	360
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)