



HSTPYL125025FRL, Heat Shrink Tubing, Thin Wall, Yellow

By Burndy
Catalog # [HSTPYL125025FRL](#)

1.25" ID Min (Issued), .625" ID Max (Recovered), Thin Wall, Yellow,
25-Foot Reel

Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

Dimensions

Height 0.035 in



Width 1.25 in
Length 300 in
Dimensions 300 in x 1.25 in x 0.035 in

General

Color Yellow
UPC 621945696839

Logistics

Carton Quantity 4

Product Assets

[Catalog \[English\]](#)