



HSW100T48PF, Heat Shrink Tubing, Thin Wall, White

By Burndy
Catalog # [HSW100T48PF](#)

1" ID Min (Issued), .50" ID Max (Recovered), Thin Wall, White, 4-Foot Reel

Features

- Heat Shrink Tubing
- 1" ID Min (Exp), .5" ID Max (Rec)
- 2/0-300, Polyolefin, Thin Wall, White
- Shrink Ratio 2:1
- 4 Foot Reel

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM

Conductor

Conductor Range	#2/0 AWG - 300 Kcmil
Conductor Size	2/0AWG - 300kcmil

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Width	1 in
Height	1 in
Length	48 in
Dimensions	48 in x 1 in x 1 in

General

Material	Cross-linked Polyolefin
UPC	781810212912
Color	White

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)