



HSW14FR, Heat Shrink PVC, Thin Wall, Flame Rtrdnt, White

By Burndy
Catalog # [HSW14FR](#)



.25" ID Min (Issued), .13" ID Max (Recovered), Fire Retardant, Thin Wall, White, 50-Foot Reel

Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	

Conductor

Conductor Range	#12 AWG to #10 AWG
Conductor Size	12AWG -8AWG

Configuration

Connector Type	THIN WALL TUBES/REELS
----------------	-----------------------

Dimensions

Width	0.25 in
Height	0.25 in
Length	600 in
Dimensions	600 in x 0.25 in x 0.25 in

General

Material	Polyvinyl chloride
UPC	781810266908
Color	White

Logistics

Minimum Pack Quantity	48
-----------------------	----

Product Assets

[Catalog \[English\]](#)