



HSW14T48PF, Heat Shrink Tubing, Thin Wall, White

By Burndy
Catalog # [HSW14T48PF](#)

.25" ID Min (Issued), .125" ID Max (Recovered), Thin Wall, White, 4-Foot Reel

Features

- Heat Shrink Tubing
- .25" ID Min (Exp), .125" ID Max (Rec)
- #14-#10, Polyolefin, Thin Wall, White, 600 V
- Shrink Ratio 2:1
- 4 Foot Reel

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	Yes
UL Listed	No

Conductor

Conductor Size	14AWG - 10AWG
Conductor Range	#12 AWG to #10 AWG

Configuration

Connector Type	THIN WALL REEL
Dimensions	
Length	48 in
Width	0.25 in
Height	0.25 in
Dimensions	48 in x 0.25 in x 0.25 in

General

Color	White
Material	Cross-linked Polyolefin
UPC	781810212592

Logistics

Minimum Pack Quantity	1
Carton Quantity	10
Pallet Quantity	4000

Product Assets

[Catalog \[English\]](#)