



HSY100FR, Heat Shrink Tubing, Thin Wall, Yellow

By Burndy
Catalog # [HSY100FR](#)



1" ID Min (Issued), .50" ID Max (Recovered), Fire Retardant, Thin Wall, Yellow, 25-Foot Reel

Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM

Conductor

Conductor Range	#1/0 AWG to #4/0 AWG
Conductor Size	4/OAWG - 300kcmil

Configuration

Connector Type	THIN WALL TUBES/REELS
----------------	-----------------------

Dimensions

Width	1 in
Height	1 in
Length	600 in
Dimensions	600 in x 1 in x 1 in

General

Material	Polyvinyl chloride
UPC	781810266984
Color	Yellow

Logistics

Minimum Pack Quantity	1
Carton Quantity	16
Pallet Quantity	128

Product Assets

[Catalog \[English\]](#)