



HSY12T300PF, Heat Shrink Tubing, Thin Wall, Yellow

By Burndy
Catalog # [HSY12T300PF](#)

.50" ID Min (Issued), .25" ID Max (Recovered), Thin Wall, Polyolefin, Yellow, 25-Foot Reel

Features

- Heat Shrink Tubing
- .5" ID Min (Exp), .25" ID Max (Rec)
- #6-#2, Polyolefin, Thin Wall, Yellow, 600 V
- Shrink Ratio 2:1
- 25 Foot Reel

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	

Conductor

Conductor Range	#6 AWG to #2 AWG
Conductor Size	6AWG - 2AWG

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Width	0.5 in
Height	0.5 in
Length	300 in
Dimensions	300 in x 0.5 in x 0.5 in

General

Material	Cross-linked Polyolefin
UPC	781810213827
Color	Yellow

Logistics

Minimum Pack Quantity	1
Carton Quantity	1
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)