



HSY150T48PF, Heat Shrink Tubing, Thin Wall, Yellow

By Burndy
Catalog # [HSY150T48PF](#)

1.50" ID Min (Issued), .75" ID Max (Recovered), Thin Wall, Yellow, 4-Foot Reel

Features

- Heat Shrink Tubing
- 1.5" ID Min (Exp), .75" ID Max (Rec)
- 2/0-350, Polyolefin, Thin Wall, Yellow, 600 V
- Shrink Ratio 3:1
- 4 Foot Reel

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM

Conductor

Conductor Range	#2/0 AWG - 350 Kcmil
Conductor Size	250kcmil - 500kcmil

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Width	1.5 in
Height	1.5 in
Length	48 in
Dimensions	48 in x 1.5 in x 1.5 in

General

Material	Cross-linked Polyolefin
UPC	781810212981
Color	Yellow

Logistics

Minimum Pack Quantity	1
Carton Quantity	1
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)