



HSY200T48PF, Heat Shrink Tubing, Thin Wall, Yellow

By Burndy
Catalog # [HSY200T48PF](#)

2" ID Min (Issued), 1" ID Max (Recovered), Thin Wall, Yellow, 4-Foot Reel

Features

- Heat Shrink Tubing
- 2" ID Min (Exp), 1" ID Max (Rec)
- 250-500, Polyolefin, Thin Wall, Yellow, 600 V
- Shrink Ratio 2:1
- 4 Foot Reel

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM

Conductor

Conductor Range	250-500 Kcmil
Conductor Size	350kcmil - 750kcmil

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Width	2 in
Height	2 in
Length	48 in
Dimensions	48 in x 2 in x 2 in

General

Material	Cross-linked Polyolefin
UPC	781810213063
Color	Yellow

Logistics

Minimum Pack Quantity	1
Carton Quantity	1
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)