



HSY316T300PF, Heat Shrink Tubing, Thin Wall, Yellow

By Burndy
Catalog # [HSY316T300PF](#)

.19" ID Min (Issued), .09" ID Max (Recovered), Thin Wall, Polyolefin, Yellow, 25-Foot Reel

Features

- Heat Shrink Tubing
- .19" ID Min (Exp), .09" ID Max (Rec)
- #18-#12, Polyolefin, Thin Wall, Yellow, 600 V
- Shrink Ratio 2:1
- 25 Foot Reel

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM

Conductor

Conductor Range	#18 AWG to #12 AWG
Conductor Size	18AWG - 12AWG

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Width	0.187 in
Height	0.187 in
Length	300 in
Dimensions	300 in x 0.187 in x 0.187 in

General

Material	Cross-linked Polyolefin
UPC	781810213551
Color	Yellow

Logistics

Minimum Pack Quantity	1
Carton Quantity	1
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)