



HSY316T48PF, Heat Shrink Tubing, Thin Wall, Yellow

By Burndy
Catalog # [HSY316T48PF](#)

.19" ID Min (Issued), .09" ID Max (Recovered), Thin Wall, Yellow, 4-Foot Reel

Features

- Heat Shrink Tubing
- .19" ID Min (Exp), .09" ID Max (Rec)
- #18-#12, Polyolefin, Thin Wall, Yellow, 600 V
- Shrink Ratio 2:1
- 4 Foot Reel

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	

Conductor

Conductor Range	#18 AWG to #12 AWG
Conductor Size	18AWG - 12AWG

Configuration

Connector Type	THIN WALL REEL
Dimensions	
Width	0.187 in
Height	0.187 in
Length	48 in
Dimensions	48 in x 0.187 in x 0.187 in

General

Material	Cross-linked Polyolefin
UPC	781810212493
Color	Yellow

Logistics

Minimum Pack Quantity	1
Carton Quantity	1
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)