



HSY38T48PF, Heat Shrink Tubing, Thin Wall, Yellow

By Burndy
Catalog # [HSY38T48PF](#)

.38" ID Min (Issued), .19" ID Max (Recovered), Thin Wall, Polyolefin, Yellow, 4-Foot Reel

Features

- Heat Shrink Tubing
- .38" ID Min (Exp), .19" ID Max (Rec)
- #8-#6, Polyolefin, Thin Wall, Yellow
- Shrink Ratio 2:1
- 4 Foot Reel

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM

Conductor

Conductor Range	#8 AWG to #6 AWG
Conductor Size	8AWG - 6AWG

Configuration

Connector Type	THIN WALL REEL
Dimensions	
Width	0.375 in
Height	0.375 in
Length	48 in
Dimensions	48 in x 0.375 in x 0.375 in

General

Material	Cross-linked Polyolefin
UPC	781810212639
Color	Yellow

Logistics

Minimum Pack Quantity	1
Carton Quantity	1
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)