



HYAOF39, Dual Rated High Capacity Limiter

By Burndy
Catalog # [HYAOF39](#)

High Capacity Limiter, Bus to Cable

Features

- High Capacity Bus to 750 kcmil cable - up to 600V

Specifications

Certification - CSA Approved No

Conductor

Conductor - AL Str Size	750 kcmil
Conductor - AL Str Size Range	750 kcmil
Conductor - Copper Str Size	750 kcmil

Configuration

Physical Attribute - Number of Holes	2
Connector Type	Limiter

Dimensions

Dimension - Pad Width inch	51 in
Dimension - Bolt Size fraction	1/2



Dimension - B Length fraction	2-1/2 in
Dimension - B Length inch	2.50 in
Dimension - D inch	2 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	1.31 in

General

Die Index	24
UPC	621945465763
UPC 12 Digit	621945433366
UPC 14 Digit GTIN	006219454333666

Logistics

Minimum Pack Quantity	20
Pallet Quantity	90
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)