

HYMS34, High Capacity Limiter, Cable to Mole

By Burndy
Catalog # [HYMS34](#)

High Capacity Limiter - Cable to Mole

Features

- High Capacity Limiter - Cable to Mole
- 500 kcmil Cable, 200,000A - 600V

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	500 kcmil
-----------------------------	-----------

Configuration

Physical Attribute - Number of	4
Crimps Required	
Connector Type	Limiter

Dimensions



Dimension - P inch	0.81 in
Dimension - B Length inch	1.88 in
Dimension - Hole Size inch	0.56 in

General

Plated	N
Die Index	20
UPC	621945465817
Plating Type	Unplated
UPC 12 Digit	781810803158
UPC 14 Digit GTIN	007818108031588

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1080
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)