

J1252, Copper Bail, Tin Plated

By Burndy
Catalog # J1252



Tin plated, hard drawn copper bail designed to make hot-line clamp adapter using HYCRIMP, CABELOK, CRIMPIT or Figure 6-shaped CRIMPIT connectors.

Features

- Designed to make hot-line clamp adapter using HYCRIMP, CABELOK CRIMPIT, or Figure 6-Shaped CRIMPIT Connectors (sold separately)
- Where hot sticks are used, the CABELOK CRIMPIT or Figure 6-Shaped CRIMPIT are recommended (sold separately)
- The line can be approached with the connector and bail held in the tool
- Bails are tin-plated hard drawn copper

Application

Designed To Make Hot-Line Clamp Adapter Using HYCRIMP, CABELOK CRIMPIT Or Figure 6 -Shaped CRIMPIT Connectors

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil
-------------------------	---

Conductor - AL Str Size Range	• 400 kcmil
Conductor - ACSR Str Size	2/0 AWG-400 kcmil
Conductor - ACSR Str Size Range	397.5 (18/1) Chickadee kcmil

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Length	4.25 in
Dimension - Height inch	4.25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Height	4.06 in
Width	0.38 in
Diameter	0.38 in
Dimensions	4.25 in x 0.38 in x 4.06 in

General

Plated	Y
Sub Brand	CONNECTOR
UPC	781810014097
Type	Bail
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810014097
UPC 14 Digit GTIN	00781810014097

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2400
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)