



K10P4CG1, Copper Neutral Bar, 10 Outlets

By Burndy
Catalog # [K10P4CG1](#)

Copper Neutral Bar, #14-4 AWG, Line: #6-14 AWG, 10 Outlets,
Steel Zinc Plated Bolt



Features

- Copper Neutral Bar
- 10 Outlets
- Steel Zinc Plated Bolt Material

Specifications

Certification - ETL	No
Standards - RoHS Compliance	UI
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor Range	#4 AWG to #14 AWG
-----------------	-------------------

Configuration

Connector Type	Neutral Bar
----------------	-------------

Dimensions

Dimension - Width inch	0.35 in
Dimension - Width mm	9 mm

Dimension - L Length Overall	131 mm
mm	
Dimension - Height inch	.48 in
Length	5.16 in
Dimension - Hole Size mm	12 mm
Dimension - Length Overall	5.16 in
inch	
Width	0.35 in
Height	0.48 in
Dimensions	5.16 in x 0.35 in x 0.48 in

General

Material - Bolt	Steel Zinc Plated
Material	Copper
UPC	781810355497

Logistics

Minimum Pack Quantity	500
Carton Quantity	150
Pallet Quantity	9600

Product Assets

[Catalog \[English\]](#)