




K14P4CG1, Copper Neutral Bar, 14 Outlets

By Burndy
Catalog # [K14P4CG1](#)



Copper neutral bar, high strength electrolytic copper, Line: #14-4
AWG, Circuit: #6-14 AWG, 14 Outlets

Features

- Copper Neutral Bar
- #14-4 AWG Cu, 14 Outlets

Specifications

Certification - ETL	No
Standards - RoHS Compliance Status	UI
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor Range	#4 AWG to #14 AWG
-----------------	-------------------

Configuration

Connector Type	Neutral Bar
----------------	-------------

Dimensions

Dimension - Width inch	0.35 in
Dimension - Width mm	9 mm
Dimension - L Length Overall mm	171 mm

Dimension - Height inch	.48 in
Length	6.75 in
Dimension - Hole Size mm	12 mm
Dimension - Length Overall inch	6.74 in
Width	0.35 in
Height	0.48 in
Dimensions	6.75 in x 0.35 in x 0.48 in

General

Material - Bolt	Steel Zinc Plated
Material	Copper
UPC	781810125328

Logistics

Minimum Pack Quantity	1
Carton Quantity	144
Pallet Quantity	1200

Product Assets

[Catalog \[English\]](#)