



K15P4CAG1, AL Neutral Bar, 15 Circuits, Dual Rated

By Burndy
Catalog # [K15P4CAG1](#)

Aluminum neutral bar, 6061-T6 aluminum alloy, tin plated, 15 Circuits, #14-4 AWG



Features

- Aluminum Neutral Bar Assembly
- Zinc Plated Steel Bolt

Specifications

Certification - ETL	No
Certification - UL Recognized	Yes
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Range	#4 AWG to #14 AWG
-----------------	-------------------

Configuration

Connector Type	Aluminum Neutral Bar Assembly
----------------	-------------------------------

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Package Height	2.300 in
Dimension - Height mm	11.2 mm
Length	5.39 in
Dimension - Height inch	0.44 in

Package Weight	3.240 lb.
Dimension - Width mm	8 mm
Dimension - Width inch	0.31 in
Package Length	8.100 in
Package Width	3.400 in
Dimension - L Length Overall mm	137 mm
Height	0.44 in
Width	0.31 in
Dimension - Length Overall inch	5.39 in
Dimensions	5.39 in x 0.31 in x 0.44 in

General

Plated	N
Material - Bolt	Steel Zinc Plated
UPC	781810665565
Insulation	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810665565
UPC 14 Digit GTIN	00781810665565

Logistics

Minimum Pack Quantity	1
Pallet Quantity	12000
Carton Quantity	150

Product Assets

[Catalog \[English\]](#)