



K21A39U2N, AL Universal Terminal, 3-Conductor, 2-Hole

By Burndy
Catalog # [K21A39U2N](#)

3 Conductor, 1/0 AWG-750 kcmil, 2-Hole, 1/2" holes, 1-3/4" Spacing, tin plated

Features

- AL9CU Dual Rated for both copper an aluminum conductor
- Listed to UL Wire Connector Standard UL486A-486B
- 1/2" diameter stud holes spaced 1-3/4" on center (NEMA-spacing)
- Range Taking conductor port

Application

Terminate multiple conductors onto equipment pads, panel boards, or switchgear

Specifications

Certification - CSA Approved	Yes
UL Listed	Yes
Standards - RoHS Compliance	CM
Status	

Configuration

Connector Type	Stacked
----------------	---------



Dimensions

Width	2.75 in
Height	3 in
Length	5.34 in
Dimension - Bolt Size fraction	1/2
Dimensions	5.34 in x 2.75 in x 3 in

General

Type	Bolted Lugs & Terminals
Material	Aluminum
UPC	621945510180

Logistics

Minimum Pack Quantity	1
Carton Quantity	18
Pallet Quantity	576

Product Assets

[Catalog \[English\]](#)