




K2C20B1TN, SERVIT POST Mech Connector, 2 Cables to Flat

By Burndy
Catalog # [K2C20B1TN](#)



2 Cables to Flat, #10-#5 Str Copper or #10-#4 Solid Copper,
5/16" Stud, Tin Plated

Features

- SERVIT POST mechanical connector used to ground 1 or 2 cables to steel structures, fence posts, and transformers
- Also used to tap 1 or 2 cables from bus bar
- 1-Wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG
Conductor - Copper Solid Size Range	10 AWG-4 AWG
Physical Attribute - Number of Conductors Accommodated Total	2
Conductor - Copper Str Size Range	10 AWG-5 AWG
Conductor - Copper Str Size	• 10 AWG • 9 AWG • 8 AWG

- 7 AWG
- 6 AWG
- 5 AWG

Dimensions

Dimension - Height mm	26.9 mm
Dimension - Height inch	1.06 in
Dimension - Body Width inch	0.50 in
Dimension - P inch	0.22 in
Dimension - L Length Overall mm	52 mm
Dimension - B Length inch	0.85 in
Dimension - Nut Width inch	0.69 in
Dimension - D inch	1.00 in
Dimension - Length Overall inch	2.06 in

Force Related

Stud Installation Torque inch pounds	180 LBS/in
--------------------------------------	------------

General

Plated	Y
Trade Name	SERVIT POST™
UPC	781810512906
Type	KC and K2C Series
Material	Bronze Alloy, Leaded
Plating Type	Tin Plated
UPC 12 Digit	781810512906
UPC 14 Digit GTIN	00781810512906

Logistics

Minimum Pack Quantity	1
Pallet Quantity	19800
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)