



K3A36U4N, AL Universal Terminal, 3-Conductor, 4-Hole

By Burndy
Catalog # [K3A36U4N](#)

3-Conductor, 4-Hole, 1/2" Stud, 1.75" Spacing, #2 AWG-600 kcmil, Tin Plated



Features

- Dual rated lugs
- Constructed from high strength aluminum alloy
- Electro tin plating proving low contact resistance

Application

For Aluminum and Copper Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	EX
Status	
Certification - UL Listed Direct	No
Burial	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil • 550 kcmil • 556 kcmil • 600 kcmil
Conductor - AL Str Size Range	2 Str. - 600 Kcmil
Conductor - Copper Str Size	• 2 AWG • 1 AWG

	• 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil
Conductor Size	2 AWG-600 KCMIL
Number Of Conductors	3
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	2 Str. - 600 Kcmil

Configuration

Physical Attribute - Number of Screws	3
Physical Attribute - Number of Holes	4
Connector Type	Parallel Set-Screw

Dimensions

Dimension - Pad Width inch	3.64 in
Package Height	2.200 in
Dimension - Height mm	39.6 mm
Dimension - Hole Size fraction	9/16
Dimension - Height inch	1.56 in
Dimension - Height fraction	1.5555555555555556 in
Package Weight	2.130 lb.
Package Length	6.450 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	5.900 in
Dimension - L Length Overall mm	119.12 mm
Dimension - Width fraction	3-63/100 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Stud Size inch	1/2 in
Dimension - Bolt Hole Size inch	0.57 in
Dimension - Bolt Size fraction	1/2
Dimension - Width inch	3.64 in
Dimension - D inch	3.22 in

Dimension - N inch 0.63 in
Dimension - Length Overall inch 4.69 in

Force Related

Installation Torque Recommended 375 LBS/in
in-lb

General

Product Family MECHANICAL
Material - Hardware Aluminum
Physical Attribute - Screw Type Slot
Plated Yes
Sub Brand UNIVERSAL TERM
Product Type Terminal
UPC 781810601228
Type Bolted Lugs & Terminals

Material Aluminum
Plating Type Tin
UPC 12 Digit 781810601228
UPC 14 Digit GTIN 00781810601228

Logistics

Minimum Pack Quantity 1
Pallet Quantity 36
Carton Quantity 36

Operational

Temperature Rating 194

Product Assets

[Catalog \[English\]](#)



A Hubbell brand