



K6B28262N, Cu, Multiple Outlet
Transformer Term, Lg Groove: #6-4/0
AWG, Sm Groove: #6 Str-2/0 AWG, 2-Hole,
1/2" Stud, 1.75" Spacing

By Burndy
Catalog # [K6B28262N](#)

Cast Cu Alloy URD Multiple Transformer Terminal, 2-NEMA Holes,
#6 - 4/0 AWG (Large Groove) #6 Str - 2/0 AWG (Small Groove),
9/16" Hole Dia.

Features

- 2-NEMA Holes

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	6 AWG-4/0 AWG
Conductor - Copper Str Size	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG

Configuration

Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.15 in
Package Height	0.000 in
Dimension - Hole Size fraction	14/25
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - D inch	3.19 in
Dimension - N inch	0.62 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	7.75 in

General

Trade Name	KA-LUG™
Material - Hardware	Brass
UPC	781810189108
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810189108
UPC 14 Digit GTIN	00781810189108

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)