



K6B284N, Cu, Underground Multiple Outlet Transformer Term, #6-4/0 Str AWG, 4-Holes, 1/2" Stud, 1.75" Spacing, 6 Outlets

By Burndy
Catalog # [K6B284N](#)

Cast Cu Alloy URD Transformer Terminals(NEMA Tongue), 4 Holes, #6 - 4/0 Str AWG Cu Cable (6 Outlets)

Features

- 4 NEMA Holes

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	6 AWG-4/0 AWG
Conductor - Copper Str Size	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG

Configuration

Physical Attribute - Number of Holes	4
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3 in
Package Height	0.000 in
Dimension - Hole Size fraction	14/25
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - D inch	3.19 in
Dimension - N inch	0.62 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	8.12 in

General

Trade Name	KA-LUG™
Material - Hardware	Brass
UPC	781810189153
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810189153
UPC 14 Digit GTIN	00781810189153

Logistics

Minimum Pack Quantity	1
Pallet Quantity	750
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)