



KA25H, Cu Mechanical Set Screw Lug, #4-1/0 Str, 3/8 Stud

By Burndy
Catalog # [KA25H](#)

Mechanical Set Screw Terminal for Cu, Accommodates #4-1/0 Str, 3/8" Stud

Features

- Mechanical Terminal for Copper
- #4 - 1/0 Str Copper, 3/8" Stud
- 600V Minimum Voltage Rating
- UL Listed

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Number Of Wires	1
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	# 4 Str. - 1/0 Str.

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Terminal

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Dimension - Pad Width inch	0.75 in
Package Height	0.000 in

Dimension - Height mm	0 mm
Length	1.69 in
Dimension - Height inch	0.94 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	43 mm
Height	0.94 in
Width	0.75 in
Dimension - N inch	0.38 in
Dimension - Mounting	1/2 in
Hardware Bolt Size inch	
Dimension - Hole Size mm	11 mm
Dimension - Hole Size inch	0.42 in
Dimension - Length Overall inch	1.63 in
Dimensions	1.69 in x 0.75 in x 0.94 in

General

Physical Attribute - Screw Type	Allen
UPC	781810528396
Type	Bolted Lugs & Terminals
Material	Copper
UPC 14 Digit GTIN	00781810528396

Logistics

Minimum Pack Quantity	100
Pallet Quantity	12000
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)