



KA28H, Cu Mounting Set Screw Lug, 1-Hole, 5/8" Stud

By Burndy
Catalog # [KA28H](#)



Mechanical Terminal For Copper, Mounting Set Screw Lug, 1-Hole, 5/8" Stud, #1 Str - 4/0 Str.

Features

- Copper Set Screw Terminal
- #1-4/0 Str Copper, 3/8" Stud
- Temperature Range: 194F
- 600V Minimum Voltage Rating

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Number Of Wires	1
Conductor - Copper Str Size Range	# 1Str. - 4/0 Str.

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Terminal

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Dimension - Pad Width inch	0.94 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Length	1.94 in

Dimension - Height inch	1.25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	49 mm
Dimension - B Length inch	0.81 in
Height	1.25 in
Width	0.94 in
Dimension - N inch	0.44 in
Dimension - Hole Size mm	11 mm
Dimension - Hole Size inch	0.42 in
Dimension - Length Overall inch	1.94 in
Dimensions	1.94 in x 0.94 in x 1.25 in

General

Physical Attribute - Screw Type	Allen
UPC	781810528402
Type	Bolted Lugs & Terminals
Material	Copper
UPC 14 Digit GTIN	00781810528402

Logistics

Minimum Pack Quantity	100
Pallet Quantity	400
Carton Quantity	25

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)