



KA29UG12, AL Set Screw Terminal, Dual Rated, 1-Hole

By Burndy
Catalog # [KA29UG12](#)

AL Set Screw, Universal Terminal, #2 Str-250 kcmil, 3/8" Stud, Dual Rated

Features

- Dual rated panelboard lugs constructed from high strength extruded aluminum alloy , electro tin-plated to provide low contact resistance

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	Yes

Conductor

Number Of Wires	1
Conductor - AL Str Size Range	6 Str. - 250 Kcmil
Conductor Type	- CU C Str-Size - AL C Str-Size
Conductor - Copper Str Size Range	6 Str. - 250 Kcmil

Configuration

Physical Attribute - Number of Holes	1
--------------------------------------	---

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Height inch	1.14 in

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	51 mm
Dimension - D inch	.94 in
Dimension - Hole Size mm	11 mm
Dimension - Hole Size inch	0.42 in
Dimension - Length Overall inch	2.00 in

General

Physical Attribute - Screw Type	Allen
Plated	Y
UPC	781810495087
Type	Bolted Lugs & Terminals
Material	Aluminum
Plating Type	Tin Plated
UPC 14 Digit GTIN	00781810495087

Logistics

Pallet Quantity	15750
Carton Quantity	25

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)