



KA30226U, AL Set Screw Connector, 1 or 2-Conductors, 2-Hole

By Burndy
Catalog # [KA30226U](#)



AL Set Screw Connector, 2 Conductor, Range if ONE Conductor:
#2 Str-300 kcmil; if TWO Conductors: #4 Str-1/0, Dual Rated

Features

- Dual Rated Panelboard Lugs
- High strength extruded aluminum alloy
- Electro tin-plated for low contact resistance
- Rated to 35kV

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	2 Str. - 300 Kcmil or (2) 4 Str. - 1/0 Str.

Configuration

Connector Type	Terminal
----------------	----------

Dimensions

Package Height	2.300 in
Dimension - Height mm	38.1 mm
Dimension - Bolt Size fraction	5/16
Length	2.31 in
Dimension - Height inch	1.50 in
Package Weight	2.600 lb.
Dimension - Width mm	22 mm
Dimension - Width inch	0.85 in

Package Length	10.200 in
Package Width	3.500 in
Dimension - L Length Overall mm	59 mm
Height	1.5 in
Width	0.85 in
Dimension - D inch	1.31 in
Dimension - N inch	0.25 in
Dimension - Length Overall inch	2.31 in
Dimension - Stud Size inch	5/16
Dimensions	2.31 in x 0.85 in x 1.5 in

Force Related

Installation Torque	275 LBS/in
Recommended in-lb	

General

Plated	Y
UPC	781810654507
Type	Bolted Lugs & Terminals
Material	Aluminum
Plating Type	Tin - Electro Plated
UPC 14 Digit GTIN	00781810654507

Logistics

Minimum Pack Quantity	1
Pallet Quantity	5400
Carton Quantity	150

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)