



KA34H, Copper Terminal, 1-Hole, 1/2" Stud

By Burndy
Catalog # [KA34H](#)

Copper Terminal, 4/0 Str-500 kcmil, 1-Hole, 1/2" Stud, 375 in-lbs recommended torque

Features

- Mechanical Terminal for Copper
- 4/0 AWG Str - 500 kcmil
- 1/2" Stud, UL Listed
- Temperature Rating: 194F

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	No

Configuration

Connector Type	Terminal
----------------	----------

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Length	2.55 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Height	2.09 in
Width	1.38 in
Dimensions	2.55 in x 1.38 in x 2.09 in

General

Plated	N
UPC	781810536230
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810536230

Logistics

Minimum Pack Quantity	18
Pallet Quantity	1
Carton Quantity	1

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)