



KA8C, Copper Mechanical Terminal, 1-Hole

By Burndy
Catalog # [KA8C](#)

Compact Copper Terminal, 1 Hole, 14 AWG (Sol)-8 AWG (Str), #10 Stud,
1 Screw

Features

- Compact, high copper alloy terminal for joining cable to equipment pads or terminal blocks

Application

For Joining A Wide Range Of Copper Cable To Equipment Pads Or
Terminal Blocks

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	EX
Status	
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Size	14-8 AWG
Conductor - Copper Solid Size	• 14 AWG • 13 AWG • 12 AWG • 11 AWG • 10 AWG • 9 AWG • 8 AWG
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	# 14 Sol. - # 8 Str.

Configuration

Connector Type	Terminal
----------------	----------

Dimensions

Dimension - Pad Width inch	0.38 in
----------------------------	---------

Package Height	0.000 in
Dimension - Height mm	15.5 mm
Dimension - Hole Size fraction	7/32
Dimension - Height inch	15.42 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	20.6 mm
Dimension - Hole Size mm	5.3 mm
Dimension - Hole Size inch	0.21 in
Dimension - Bolt Size fraction	#10
Dimension - Width mm	9.70 mm
Dimension - Width inch	0.38 in
Dimension - N inch	0.19 in
Dimension - Mounting Hardware Bolt Size inch	12.24 UNC
Dimension - Length Overall inch	0.81 in

General

Product Family	MECHANICAL
Material - Hardware	Steel
Physical Attribute - Screw Type	Flat head round tip
Plated	No
Sub Brand	KA-LUG
Product Type	Terminal
UPC	781810362051
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Unplated
Hardware Type	#12
UPC 14 Digit GTIN	00781810362051

Logistics

Minimum Pack Quantity	1
Pallet Quantity	96000
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)