



KA8CH, Cu Set Screw Lug, #14 Sol-#8 Str  
Cu, #10 Stud

By Burndy  
Catalog # [KA8CH](#)

KA8CH, #14 Solid - #8 Stranded Copper; #10 Stud; 45 in-lb  
recommended torque

Features

- Bolted Copper Terminal Lug
- #14 Sol - #8 Str Copper, #10 Stud
- Temperature Rating: 194F
- 600V Minimum Voltage Rating

Specifications

|                               |    |
|-------------------------------|----|
| Certification - ETL           | No |
| Certification - UL Recognized | No |
| Standards - RoHS Compliance   | UI |
| Status                        |    |
| Certification - cULus         | No |
| UL Listed                     | No |
| Certification - CSA Approved  | No |

Configuration

|                |          |
|----------------|----------|
| Connector Type | Terminal |
|----------------|----------|

Current

|                          |     |
|--------------------------|-----|
| Rating - Minimum Voltage | 600 |
|--------------------------|-----|

Dimensions

|                       |      |
|-----------------------|------|
| Dimension - Height mm | 0 mm |
|-----------------------|------|

General

|                   |                         |
|-------------------|-------------------------|
| Plated            | N                       |
| Trade Name        | KA-LUG™                 |
| UPC               | 781810528358            |
| Type              | Bolted Lugs & Terminals |
| Material          | Copper                  |
| Plating Type      | Unplated                |
| UPC 12 Digit      | 781810528358            |
| UPC 14 Digit GTIN | 00781810528358          |

Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 100 |
|-----------------------|-----|

Operational

|                    |     |
|--------------------|-----|
| Temperature Rating | 194 |
|--------------------|-----|

Product Assets

[Catalog \[English\]](#)