



KAPO750, Mechanical Pin Adaptor, Dual Rated, Offset Pin

By Burndy
Catalog # [KAPO750](#)

Mechanical Offset Pin Adaptor, Wire Range: 750 kcmil, Dual Rated, 600 V

Features

- AL9CU Dual Rated for both copper an aluminum conductor
- Listed to UL Wire Connector Standard UL486A-486B
- Rated for use with Fine Strand Conductor
- 600 Volt Rated
- Range Taking conductor port
- Plastisol insulated covers provided with each connector

Application

Terminate "upsized" conductor and/or fine strand conductor into mechanical connectors found in molded case circuit breakers, panel board equipment, and other switchgear.

Specifications

Buy American Compliant No

Conductor

Conductor - Copper DLO Size Range	350 kcmil - 750 kcmil
Conductor Size	350-750 KCMIL
Conductor - Copper Flex K Size Range	350 kcmil - 750 kcmil
Conductor - AL Str Size Range	350 kcmil - 750 kcmil
Conductor - Copper Str Size Range	350 kcmil - 750 kcmil
Conductor - Copper Flex H Size Range	350 kcmil - 750 kcmil
Conductor - Copper Flex I Size Range	350 kcmil - 750 kcmil

Configuration

Connector Type Offset

Current



Amperage Rating 535 A

Dimensions

Package Height	0.000 in
Length	4.46 in
Package Weight	0.000 lb.
Package Length	0.000 in
Outside Diameter	1.75 in
Package Width	0.000 in
Height	2.37 in
Width	1.87 in
Dimension - Strip Length inch	2.30 in
Dimensions	4.46 in x 1.87 in x 2.37 in

Force Related

Installation Torque Recommended 500 in-lb

General

Sub Brand	Pin Adaptor
UPC	621945493377
Type	• 350 - 750 Mechanical Pin Adaptor • Off-Centered Pin
Hex Key	1/2 in
Material	Aluminum

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1000
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)