



KASB28U2N, QIKSHEAR™ Series, Shear Bolt Lug, 2-hole

By Burndy
Catalog # [KASB28U2N](#)

Mechanical Shear Bolt Lug, Wire Range: 2/0 - 4/0 AWG, 2 Holes, 1/2" Stud, 1.75" Spacing



Features

- No Tooling or Die Investment Required, no crimp tools necessary
- Dual Rated AL9CU for use with both copper and aluminum conductor
- cULus Listed Wire Connector to UL486A-486B
- Up to 35kV voltage rating
- Tin Plated aluminum connectors and bolts reduce galvanic corrosion and oxide build up
- Range-taking capabilities on most sizes

Specifications

Buy America(n) Qualified BABA Compliant (All status valid till December 2026)

Dimensions

Package Length 0.000 in
Package Width 0.000 in

Package Weight 0.000 lb.
Width 1.1 in
Height 1.35 in
Package Height 0.000 in
Length 5.85 in
Dimensions 5.85 in x 1.1 in x 1.35 in

General

Type Bolted Lugs & Terminals
Series QIKSHEAR™ Series
UPC 621945658899

Logistics

Carton Quantity 14
Pallet Quantity 3276

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)