



KASB28U38, QIKSHEAR™ Series, Shear Bolt Lug, 1-hole

By Burndy
Catalog # [KASB28U38](#)

Mechanical Shear Bolt Lug, Wire Range: 2/0 - 4/0 AWG, 1-Hole, 3/8" Stud

Features

- No Tooling or Die Investment Required, no crimp tools necessary
- Dual Rated AL9CU for use with both copper and aluminum conductor
- cULus Listed Wire Connector to UL486A-486B
- Up to 35kV voltage rating
- Tin Plated aluminum connectors and bolts reduce galvanic corrosion and oxide build up
- Range-taking capabilities on most sizes

Dimensions

Height	1.35 in
Width	1.1 in
Package Height	0.000 in



Length	3.89 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimensions	3.89 in x 1.1 in x 1.35 in

General

UPC	621945658714
Type	Bolted Lugs & Terminals
Series	QIKSHEAR™ Series

Product Assets

[Catalog \[English\]](#)