



KASB34U12, QIKSHEAR™ Series, Shear Bolt Lug, 1-hole

By Burndy
Catalog # [KASB34U12](#)

Mechanical Shear Bolt Lug, Wire Range: 350-500 kcmil, 1-Hole, 1/2" Stud

Features

- No Tooling or Die Investment Required, no crimp tools necessary
- Dual Rated AL9CU for use with both copper and aluminum conductor
- cULus Listed Wire Connector to UL486A-486B
- Up to 35kV voltage rating
- Tin Plated aluminum connectors and bolts reduce galvanic corrosion and oxide build up
- Range-taking capabilities on most sizes

Dimensions

Package Length	14.563 in
Package Width	8.313 in
Package Weight	26.000 lb.
Width	1.46 in
Height	1.85 in



Package Height	6.625 in
Length	5.19 in
Dimensions	5.19 in x 1.46 in x 1.85 in

General

Type	Bolted Lugs & Terminals
Series	QIKSHEAR™ Series
UPC	621945658844

Logistics

Carton Quantity	36
Pallet Quantity	3024

Product Assets

- [Catalog \[English\]](#)
[Installation Manual \[English\]](#)