



# KASB44U12, QIKSHEAR™ Series, Shear Bolt Lug, 1-hole

By Burndy  
Catalog # [KASB44U12](#)

Mechanical Shear Bolt Lug, Wire Size: 1000 kcmil, 1-Hole, 1/2" Stud



## Features

- No Tooling or Die Investment Required, no crimp tools necessary
- Dual Rated AL9CU for use with both copper and aluminum conductor
- cULus Listed Wire Connector to UL486A-486B
- Up to 35kV voltage rating
- Tin Plated aluminum connectors and bolts reduce galvanic corrosion and oxide build up
- Range-taking capabilities on most sizes

## Dimensions

|                |           |
|----------------|-----------|
| Package Length | 0.000 in  |
| Package Width  | 0.000 in  |
| Package Weight | 0.000 lb. |
| Width          | 1.75 in   |
| Height         | 2.11 in   |

|                |                             |
|----------------|-----------------------------|
| Package Height | 0.000 in                    |
| Length         | 5.19 in                     |
| Dimensions     | 5.19 in x 1.75 in x 2.11 in |

## General

|        |                         |
|--------|-------------------------|
| Type   | Bolted Lugs & Terminals |
| Series | QIKSHEAR™ Series        |
| UPC    | 621945646384            |

## Logistics

|                 |      |
|-----------------|------|
| Carton Quantity | 14   |
| Pallet Quantity | 1260 |

## Product Assets

- [Catalog \[English\]](#)  
[Installation Manual \[English\]](#)