



KC15NSP, SERVIT POST Mechanical Connector, Cable to Flat

By Burndy
Catalog # [KC15NSP](#)



Mechanical Connector; Cable to Flat; #12 - #9 Stranded or #12 - #8 Solid Copper.

Features

- SERVIT POST tin-plated mechanical connector used to ground 1 or 2 cables to steel structures, fence posts, and transformers
- Also used to tap 1 or 2 cables from bus bar
- 1-Wrench installation

General

Catalog Number	KC15NSP
Material	Bronze, Leaded, Commercial
Plated	N
Plating Type	Unplated
Stud Installation Torque inch pounds	80 LBS/in
Trade Name	SERVIT POST™
Type	KC and K2C Series
UPC	781810449103
UPC 14 Digit GTIN	00781810449103

Dimensions

Dimension - B Length inch	0.37 in
Dimension - Body Width inch	0.38 in
Dimension - D inch	0.50 in
Dimension - Height inch	0.69 in
Dimension - Height mm	17.5 mm
Dimension - L Length Overall mm	30 mm
Dimension - Length Overall inch	1.19 in
Dimension - Nut Width inch	0.50 in
Dimension - P inch	0.14 in

Conductor Related

Conductor - Copper Solid Size	12 AWG;11 AWG;10 AWG;9 AWG;8 AWG
Conductor - Copper Solid Size Range	12 AWG-8 AWG
Conductor - Copper Str Size	12 AWG;10 AWG;9 AWG
Conductor - Copper Str Size Range	12 AWG-9 AWG
Physical Attribute - Number of Conductors Accommodated Total	1

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX

Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	44550

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - sd055917](#)
[Specifications - KC15NSP](#)