



KC17B1NSP, SERVIT POST Mechanical Connector, Cable to Flat

By Burndy
Catalog # [KC17B1NSP](#)



Mechanical SERVIT POST™ Connector; Cable to Flat

Features

- SERVIT POST tin-plated mechanical connector used to ground 1 or 2 cables to steel structures, fence posts, and transformers
- Also used to tap 1 or 2 cables from bus bar
- 1-Wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Solid Size	10 AWG 9 AWG 8 AWG 7 AWG 6 AWG
Conductor - Copper Solid Size Range	6 AWG-10 AWG
Physical Attribute - Number of Conductors Accommodated Total	1

Conductor - Copper Str Size Range	7 AWG-10 AWG
Conductor - Copper Str Size	10 AWG 9 AWG 8 AWG 7 AWG

Dimensions

Dimension - Height mm	0 mm
Dimension - L Length Overall mm	47 mm
Dimension - Cross Flats inch	0.62 in
Dimension - Length Overall inch	1.84 in

General

Plated	N
Trade Name	SERVIT POST™
UPC	781810467701
Type	KC and K2C Series
Material	Bronze, Leaded, Commercial
Plating Type	Unplated
UPC 12 Digit	781810467701
UPC 14 Digit GTIN	00781810467701

Logistics

Minimum Pack Quantity	1
Pallet Quantity	29700
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)