

KC23B2, SERVIT POST Mechanical Connector, Cable to Flat

By Burndy
Catalog # [KC23B2](#)



Mechanical SERVIT POST™ Connector; Cable to Flat

Features

- SERVIT POST tin-plated mechanical connector used to ground 1 or 2 cables to steel structures, fence posts, and transformers
- Also used to tap 1 or 2 cables from bus bar
- 1-Wrench installation

- 7 AWG
- 6 AWG
- 5 AWG
- 4 AWG
- 3 AWG
- 2 AWG

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - Copper Solid Size Range	10 AWG-1 AWG
Physical Attribute - Number of Conductors Accommodated Total	1
Conductor - Copper Str Size Range	8 AWG-2 AWG
Conductor - Copper Str Size	• 10 AWG • 9 AWG • 8 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	26.7 mm
Dimension - Height inch	1.05 in
Package Weight	0.000 lb.
Dimension - Width mm	24 mm
Dimension - Width inch	0.94 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - P inch	0.31 in
Dimension - L Length Overall mm	39 mm
Dimension - B Length inch	0.41 in
Dimension - Cross Flats inch	0.62 in
Dimension - D inch	0.50 in
Dimension - Length Overall inch	1.55 in

General

Plated	N
Trade Name	SERVIT POST™
UPC	621945138292
Type	KC and K2C Series
Material	Bronze, Leaded, Commercial
Plating Type	Unplated
UPC 12 Digit	621945138292
UPC 14 Digit GTIN	00621945138292

Logistics

Minimum Pack Quantity	1
Pallet Quantity	14850
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)