



KC26TN, SERVIT POST Mech Conn, Cable to Flat, Tin Plated

By Burndy  
Catalog # [KC26TN](#)

SERVIT POST™ Connector; Copper Cable to Flat, #2-2/0 AWG Str or #2-2/0 AWG Solid, 1/2" Stud, Tin Plated

Features

- SERVIT POST tin-plated mechanical connector used to ground 1 or 2 cables to steel structures, fence posts, and transformers
- Also used to tap 1 or 2 cables from bus bar
- 1-Wrench installation

Specifications

|                                         |       |
|-----------------------------------------|-------|
| Certification - ETL                     | No    |
| Certification - UL Recognized           | No    |
| Standards - Industry Standards Met      | UL467 |
| Standards - RoHS Compliance Status      | EX    |
| Certification - cULus                   | No    |
| Certification - UL Listed Direct Burial | Yes   |
| Industry Standard(s)                    | UL467 |
| UL Listed                               | Yes   |
| Certification - CSA Approved            | No    |

Conductor

|                                                              |                                                                                                                               |
|--------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| Conductor - Copper Solid Size                                | <ul style="list-style-type: none"><li>• 2 AWG</li><li>• 1 AWG</li><li>• 1/0 AWG</li><li>• 2/0 AWG</li><li>• 3/0 AWG</li></ul> |
| Conductor - Copper Solid Size Range                          | 2 AWG-3/0 AWG                                                                                                                 |
| Physical Attribute - Number of Conductors Accommodated Total | 1                                                                                                                             |
| Conductor - Copper Str Size Range                            | 2 AWG-2/0 AWG                                                                                                                 |
| Conductor - Copper Str Size                                  | <ul style="list-style-type: none"><li>• 2 AWG</li><li>• 1 AWG</li><li>• 1/0</li><li>• 2/0 AWG</li></ul>                       |

Dimensions

|                                 |           |
|---------------------------------|-----------|
| Package Height                  | 0.000 in  |
| Dimension - Height mm           | 35.1 mm   |
| Dimension - Height inch         | 1.38 in   |
| Dimension - Body Width inch     | 0.88 in   |
| Package Weight                  | 0.000 lb. |
| Package Length                  | 0.000 in  |
| Package Width                   | 0.000 in  |
| Dimension - P inch              | 0.44 in   |
| Dimension - L Length Overall mm | 54 mm     |
| Dimension - B Length inch       | 0.52 in   |
| Dimension - Nut Width inch      | 1.04 in   |
| Dimension - Length Overall inch | 2.12 in   |

Force Related

|                                      |            |
|--------------------------------------|------------|
| Stud Installation Torque inch pounds | 480 LBS/in |
|--------------------------------------|------------|

General

|                   |                            |
|-------------------|----------------------------|
| Plated            | N                          |
| Trade Name        | SERVIT POST™               |
| UPC               | 781810145708               |
| Type              | KC and K2C Series          |
| Material          | Bronze, Leaded, Commercial |
| Plating Type      | Tin Plated                 |
| UPC 12 Digit      | 781810145708               |
| UPC 14 Digit GTIN | 00781810145708             |

Logistics

|                 |      |
|-----------------|------|
| Pallet Quantity | 7425 |
| Carton Quantity | 25   |

Product Assets

[Catalog \[English\]](#)