



KC28B1G17, SERVIT POST Mechanical Connector, Cable to Flat

By Burndy
Catalog # [KC28B1G17](#)

Mechanical SERVIT POST™ Connector; Cable to Flat

Features

- SERVIT POST tin-plated mechanical connector used to ground 1 or 2 cables to steel structures, fence posts, and transformers
- Also used to tap 1 or 2 cables from bus bar
- 1-Wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size Range	1 AWG-4/O AWG
Physical Attribute - Number of Conductors Accommodated Total	1

Conductor - Copper Str Size Range	1 AWG-4/O AWG
-----------------------------------	---------------

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Length	3.45 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Thread Size	1/2-13

General

Plated	N
Trade Name	SERVIT POST™
UPC	781810277553
Type	KC and K2C Series
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810277553
UPC 14 Digit GTIN	00781810277553

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)