



KC34B1NSP, SERVIT POST Mechanical Connector, Cable to Flat

By Burndy
Catalog # [KC34B1NSP](#)



Mechanical SERVIT POST™ Connector; Cable to Flat

Features

- SERVIT POST tin-plated mechanical connector used to ground 1 or 2 cables to steel structures, fence posts, and transformers
- Also used to tap 1 or 2 cables from bus bar
- 1-Wrench installation

Specifications

Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified Industry Standard(s)	Contact Manufacturer UL467
Certification - CSA Approved	No

Conductor

Physical Attribute - Number of Conductors Accommodated Total	1
Conductor - Copper Str Size Range	1-300
Conductor - Copper Str Size	1 1/0 2/0 3/0 4/0 250 300

Dimensions

Package Height	0.000 in
Dimension - Height mm	60.5 mm
Dimension - Body Width inch	1.62 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - P inch	0.85 in
Dimension - Nut Width inch	2.00 in
Dimension - Length Overall inch	4.12 in

Force Related

Stud Installation Torque inch pounds	1050 LBS/in
--------------------------------------	-------------

General

Plated	N
Trade Name	SERVIT POST™
UPC	781810219881
Type	KC and K2C Series
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810219881
UPC 14 Digit GTIN	00781810219881

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)