



KC39, SERVIT POST Mechanical Connector, Cable to Flat

By Burndy
Catalog # [KC39](#)



Mechanical SERVIT POST™ Connector; Cable to Flat

Features

- SERVIT POST tin-plated mechanical connector used to ground 1 or 2 cables to steel structures, fence posts, and transformers
- Also used to tap 1 or 2 cables from bus bar
- 1-Wrench installation

Specifications

Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
Certification - CSA Approved	No

Conductor

Physical Attribute - Number of Conductors Accommodated Total	1
Conductor - Copper Str Size	300 kcmil 350 kcmil 400 kcmil 450 kcmil 500 kcmil 550 kcmil 600 kcmil 700 kcmil 750 kcmil

Dimensions

Package Height	0.000 in
----------------	----------

Dimension - Height mm	74.7 mm
Dimension - Height inch	2.94 in
Dimension - Body Width inch	1.88 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - P inch	1.01 in
Dimension - L Length Overall mm	110 mm
Dimension - B Length inch	1.13 in
Dimension - Nut Width inch	2.62 in
Dimension - Length Overall inch	4.32 in

Force Related

Stud Installation Torque inch pounds	1700 LBS/in
--------------------------------------	-------------

General

Plated	N
Trade Name	SERVIT POST™
UPC	781810448304
Type	KC and K2C Series
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810448304
UPC 14 Digit GTIN	00781810448304

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)