



KLU175H, Cu Terminal, Offset Tongue, Range Taking, 1-Hole

By Burndy

Catalog # [KLU175H](#)

Offset Tongue Copper Terminal, 1-Hole, 3/8" Stud, #4-3/0 Str
Copper, Non-Plated, Hex Head Bolt



Features

- Range-taking design reduces SKUs required in inventory
- High conductivity copper alloy for long lasting reliable contact
- Compact design, easy to install
- Slot Robertson screw, hex head, hex socket bolt require no special installation tools

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	UI
Certification - cULus	No
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	4 AWG-3/0 AWG
Conductor - Copper Str Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	1
Connector Type	Terminal

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Dimension - Pad Width inch	0.75 in
----------------------------	---------



A Hubbell brand

Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - B Length fraction	22/31 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	56 mm
Dimension - B Length inch	0.71 in
Dimension - N inch	0.43 in
Dimension - Hole Size mm	10 mm
Dimension - Hole Size inch	0.39 in
Dimension - Length Overall inch	2.20 in
Dimension - Strip Length inch	1 in
Dimension - Stud Size inch	3/8

Force Related

Installation Torque Recommended in-lb	124 LBS/in
---------------------------------------	------------

General

Physical Attribute - Screw Type Plated	Hexagonal Bolt N
Trade Name	SCRULUG™
UPC	781810463413
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810463413
Hardware Type	3/8 UNF Socket/HexScrew
UPC 14 Digit GTIN	00781810463413

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)