


KLU175TP, Cu Terminal, Offset Tongue, Range Taking, 1-Hole

By Burndy
Catalog # [KLU175TP](#)



Offset Tongue Copper Terminal, 1-Hole, 3/8" Stud, #4-3/0 Str Copper, Tin-Plated

Features

- Range-taking design reduces SKUs required in inventory
- High conductivity copper alloy for long lasting reliable contact
- Compact design, easy to install
- Slot Robertson screw, hex head, hex socket bolt require no special installation tools

Specifications

Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG
Conductor Size	4-3/0 AWG
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	4 AWG-3/0 AWG

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	1
Connector Type	Pressure Bar

Dimensions

Dimension - Pad Width inch	0.75 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	56 mm
Dimension - Hole Size mm	10 mm
Dimension - Hole Size inch	0.39 in
Dimension - Screw Size inch	3/8
Dimension - Strip Length inch	1 in
Dimension - Stud Size inch	3/8
Dimension - Bolt Size fraction	3/8
Dimension - B Length fraction	22/31 in
Dimension - B Length inch	0.71 in
Dimension - N inch	0.43 in
Dimension - Length Overall inch	2.20 in

Force Related

Installation Torque	120
Recommended in-lb	

General

Trade Name	SCRULUG™
Physical Attribute - Screw Type	Allen
Plated	Y
UPC	781810352700
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Tin
Hardware Type	3/8 UNF Socket/HexScrew
UPC 14 Digit GTIN	00781810352700

Logistics

Minimum Pack Quantity	1000
Pallet Quantity	13920
Carton Quantity	40

Product Assets

[Catalog \[English\]](#)