



KLU25TP, Cu Terminal, Offset Tongue, Range Taking, 1-Hole

By Burndy

Catalog # [KLU25TP](#)

Copper Terminal Offset Tongue, 1-Hole, #14-#10 Sol, #6 Stud, 1
Screw, Tin Plated



Features

- Range-taking design reduces SKUs required in inventory
- High conductivity copper alloy for long lasting reliable contact
- Compact design, easy to install
- Slot Robertson screw, hex head, hex socket bolt require no special installation tools

Specifications

Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 14 AWG • 12 AWG • 10 AWG
Conductor Size	14-10 AWG
Conductor - Copper Solid Size	• 14 AWG • 13 AWG • 12 AWG • 11 AWG • 10 AWG
Conductor - Copper Solid Size Range	14 AWG-10 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor - Copper Str Size Range	14 AWG-10 AWG

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	1
Connector Type	Pressure Bar



Dimensions

Dimension - Pad Width inch	0.31 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	26 mm
Dimension - Hole Size mm	4 mm
Dimension - Hole Size inch	0.14 in
Dimension - Screw Size inch	8-32
Dimension - Strip Length inch	7/16
Dimension - Stud Size inch	#6
Dimension - Bolt Size fraction	#6
Dimension - B Length fraction	9/32 in
Dimension - B Length inch	0.28 in
Dimension - N inch	0.21 in
Dimension - Length Overall inch	1.02 in

Force Related

Installation Torque	20
Recommended in-lb	

General

Trade Name	SCRULUG™
Physical Attribute - Screw Type	Slot
Plated	Y
UPC	781810352502
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Tin
Hardware Type	No. 8-32 Slotted RoundMachine Screw
UPC 14 Digit GTIN	00781810352502

Logistics

Pallet Quantity	1
Carton Quantity	500

Product Assets

[Catalog \[English\]](#)