



## KLU300, Cu Terminal, Offset Tongue, Range Taking, 1-Hole

By Burndy

Catalog # [KLU300](#)

Copper Terminal, Offset Tongue, 1-Hole, 1/0 AWG Str-350 kcmil, 3/8"  
Stud, 1 Screw, Non-Plated



Features

- Range-taking design reduces SKUs required in inventory
- High conductivity copper alloy for long lasting reliable contact
- Compact design, easy to install
- Slot Robertson screw, hex head, hex socket bolt require no special installation tools

Application

For Joining A Wide Range Of Copper Cable To Equipment Pads Or Bar And Offset Tongue, Non-Plated

Specifications

|                                         |       |
|-----------------------------------------|-------|
| Certification - UL Recognized           | No    |
| Buy American Compliant                  | No    |
| Certification - cULus                   | Yes   |
| Industry Standard(s)                    | UL467 |
| Certification - ETL                     | No    |
| Standards - Industry Standards Met      | UL467 |
| Standards - RoHS Compliance             | CM    |
| Status                                  |       |
| Certification - UL Listed Direct Burial | No    |
| UL Listed                               | No    |
| Certification - CSA Approved            | No    |

Conductor

|                                   |                                                                                                                                                                         |
|-----------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - Copper Str Size       | <ul style="list-style-type: none"><li>• 1/0</li><li>• 2/0 AWG</li><li>• 3/0 AWG</li><li>• 4/0 AWG</li><li>• 250 kcmil</li><li>• 300 kcmil</li><li>• 350 kcmil</li></ul> |
| Conductor Size                    | 1/0 AWG-350 KCMIL                                                                                                                                                       |
| Conductor Type                    | CU C Str-Size                                                                                                                                                           |
| Conductor - Copper Str Size Range | 1/0 -350 kcmil                                                                                                                                                          |

Configuration

|                                       |              |
|---------------------------------------|--------------|
| Physical Attribute - Number of Screws | 1            |
| Physical Attribute - Number of Holes  | 1            |
| Connector Type                        | Pressure Bar |

Dimensions

|                                 |           |
|---------------------------------|-----------|
| Dimension - Pad Width inch      | 0.99 in   |
| Package Height                  | 3.250 in  |
| Dimension - Height mm           | 0 mm      |
| Package Weight                  | 2.130 lb. |
| Package Length                  | 4.750 in  |
| Package Width                   | 3.250 in  |
| Dimension - L Length Overall mm | 72 mm     |
| Dimension - Hole Size mm        | 10 mm     |
| Dimension - Hole Size inch      | 0.39 in   |
| Dimension - Screw Size inch     | 5/8       |
| Dimension - Strip Length inch   | 1-5/8     |
| Dimension - Stud Size inch      | 3/8       |
| Dimension - Bolt Size fraction  | 3/8       |
| Dimension - B Length fraction   | 1-7/32 in |
| Dimension - B Length inch       | 1.22 in   |
| Dimension - N inch              | 0.52 in   |
| Dimension - Length Overall inch | 2.83 in   |

Force Related

|                                 |           |
|---------------------------------|-----------|
| Installation Torque Recommended | 275 in-lb |
|---------------------------------|-----------|

General

|                                 |                         |
|---------------------------------|-------------------------|
| Product Family                  | MECHANICAL              |
| Trade Name                      | SCRULUG™                |
| Physical Attribute - Screw Type | Allen                   |
| Plated                          | No                      |
| Sub Brand                       | SCRULUG                 |
| Product Type                    | Terminal                |
| UPC                             | 781810351420            |
| Type                            | Bolted Lugs & Terminals |
| Material                        | Copper                  |
| Plating Type                    | Unplated                |
| Hardware Type                   | 5/8 UNF Socket/HexScrew |
| UPC 14 Digit GTIN               | 00781810351420          |

Logistics

|                       |      |
|-----------------------|------|
| Minimum Pack Quantity | 1    |
| Pallet Quantity       | 4860 |
| Carton Quantity       | 60   |

Product Assets

[Catalog \[English\]](#)



A Hubbell brand