




KPA4CUNPL, Pressure Bar Style Copper, #14 Sol-4 Str, 1-Hole

By Burndy
Catalog # [KPA4CUNPL](#)

Mech. Pressure Bar Style Copper, 1-Hole, 1/4" Stud, #14 Sol-4 Str, Unplated



Features

- High copper alloy terminal (unplated) for joining a wide range of cable to equipment pads or terminal blocks
- Tongue and body are 1-piece design, pressure bar equalizes pressure over the conductor and prevents the screw from cutting into the cable

Application

For Joining A Wide Range Of Cable To Equipment Pads Or Terminal Blocks, Especially Good In Light Industrial Applications

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size	• 14 AWG • 12 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG
Conductor Size	14-4 AWG
Conductor - Copper Str Navy Size Range	23 (7) Navy-40 (19) Navy
Conductor - Copper Str Navy Size	• 23 (7) Navy • 30 (19) Navy • 40 (19) Navy
Conductor - Copper Solid Size	• 14 AWG • 13 AWG • 12 AWG • 11 AWG

- 10 AWG
- 9 AWG
- 8 AWG
- 7 AWG
- 6 AWG
- 5 AWG
- 4 AWG

Conductor - Copper Solid Size Range 14 AWG-4 AWG

Conductor Type

- CU C Str-Size
- CU C Solid-Size

Conductor - Copper Str Size Range 14 AWG-4 AWG

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	1
Connector Type	Pressure Bar

Dimensions

Dimension - Pad Width inch	0.50 in
Package Height	0.000 in
Dimension - Height mm	23.9 mm
Dimension - Height inch	0.94 in
Dimension - Height fraction	47/50 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	31
Dimension - Hole Size mm	7 mm
Dimension - Hole Size inch	0.27 in
Dimension - Stud Size inch	1/4
Dimension - Bolt Size fraction	1/4
Dimension - Width mm	11 mm
Dimension - Width inch	0.42 in
Dimension - D inch	0.59 in
Dimension - N inch	0.3 in
Dimension - Length Overall inch	1.22

Force Related

Installation Torque Recommended 35 in-lb

General

Product Family	MECHANICAL	UPC 14 Digit GTIN	00781810006245
Trade Name	SCRULUG™		
Physical Attribute - Screw Type	Slot	Logistics	
Plated	No	Minimum Pack Quantity	1
Sub Brand	SCRULUG	Pallet Quantity	59400
Product Type	Terminal	Carton Quantity	100
UPC	781810006245		
Type	Bolted Lugs & Terminals	Product Assets	
Material	Copper	Catalog [English]	
Plating Type	Unplated		

