



KPA8CUPG10, Copper Terminal, 1-Hole, Green Screw

By Burndy
Catalog # [KPA8CUPG10](#)



Mech. Pressure Bar Stayle Copper, 1-Hole, #14 (Sol)-6 AWG (Str), #10 Stud, Green Screw

Features

- High copper alloy terminal (unplated) for joining a wide range of cable to equipment pads or terminal blocks
- Tongue and body are 1-piece design, pressure bar equalizes pressure over the conductor and prevents the screw from cutting into the cable

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	UI
Status	
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	Yes

Configuration

Connector Type	Terminal
----------------	----------

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Length	1.04 in
Dimension - Height inch	0.81 in
Package Weight	0.000 lb.
Dimension - Width mm	9.4 mm
Dimension - Width inch	0.38 in
Package Length	0.000 in
Package Width	0.000 in

Dimension - L Length Overall mm	26.4 mm
Height	0.81 in
Width	0.38 in
Dimension - Hole Size mm	5.1 mm
Dimension - Hole Size inch	0.20 in
Dimension - Length Overall inch	1.04 in
Dimension - Stud Size inch	#10
Dimensions	1.04 in x 0.38 in x 0.81 in

Force Related

Installation Torque	35
Recommended in-lb	

General

Plated	Y
Trade Name	SCRULUG™
UPC	781810043981
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Tin
UPC 14 Digit GTIN	00781810043981

Logistics

Minimum Pack Quantity	2000
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)